

# RM 734

Disinfecting cleaner, alkaline

## PRODUCT INFORMATION

**Alkaline foam cleaner with active chlorine**

### Properties:

- \* alkaline cleaning- and disinfectant agent
- \* removes oil, grease, protein soiling
- \* good cleaning action, stable foam carpet
- \* gentle to metallic, ceramic and plastic surfaces
- \* easily biodegradable according OECD
- \* applicable manual and with plastic RM-Sprayer
- \* applicable with Inno Foam Set and high pressure machine
- \* pH- value in concentrate approx. 14
- \* clear, yellowish liquid with mild odour

### Fields of application:

- \* food area
- \* butchery
- \* beverage industry
- \* agriculture
- \* sanitary areas
- \* kitchen, canteen
- \* cleaning of containers

### Processing:

	dosing	temperature	reaction time (at dosing)
* manual	2-5%	20 to 50°C	5 min (5%) to 20 min (2%)
* plastic RM- sprayer	2-5%	20 to 50°C	5 min (5%) to 20 min (2%)
* high pressure with Inno Foam Set	2-5%	cold	5 min (5%) to 20 min (2%)

Concentration and reaction-time are dependent on the soiling and degree of contamination

- Please require our certificates regarding this matter! -

### Economy:

1 L is sufficient for cleaning and disinfecting of approx. 200 m<sup>2</sup>, dosage 3%, for medium soiled areas

### Handling:

pre-dilution: first measure the necessary amount of water, then add RM 734 under stirring and mix properly.

### Remarks

- \* do not allow to dry the cleaning agent solution on surfaces
- \* we recommend the altering use with another cleaning- or disinfection agent (e.g. RM 735), to avoid the forming of resistant bacteria mutants
- \* after reaction time the disinfected surfaces and machines as well as containers, which come in contact with foods, have to rinse off with fresh water of quality of drinking water
- \* when manual applied, use protective gloves and goggles
- \* store frost-free
- \* do not mix with acids or with acid cleaner
- \* do not apply on alkali sensitive surfaces
- \* application with high pressure cleaner (HD) only with Inno Foam Set
- \* do not apply directly through the induction pipe from the cleaning agents of the high pressure cleaner
- \* do not use with RM- Sprayer made of steel or stainless steel. Danger of explosion.

# RM 734

Disinfecting cleaner, alkaline

## PRODUCT INFORMATION

### Attention:

- C Corrosive;
- R 31 Contact with acids liberates toxic gas
- R 35 Causes severe burns
  
- S 23 Do not breathe spray.
- S 26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
- S 36/37/39 Wear suitable protective clothing, gloves and eye/face protection.
- S 45 In case of accident or if you feel unwell, seek medical advice immediately (show the label where possible).
- S 50 Do not mix with acids.
- S 51 Use only in well-ventilated areas
- S 60 This material and its container must be disposed of as hazardous waste.

**Use biocides safely. Always read the label and product information before use!**

### Certificates:

- \* DVG (Deutsche Gesellschaft für Veterinärmedizin)

### Further information

- \* Material safety data sheet

### Process:

Object: e.g. butchery

- \* remove rough dirt by sweeping
- \* put on steady RM 734 with plastic- RM-Sprayer or Inno Foam Set
- \* after reaction time the disinfected surfaces and machines as well as containers, which came in contact with foods, have to rinse off with fresh water of quality of drinking water
- \* rinse machines after application with clear water